

HP-I Series

High Pressure Flowmeters

Description

The patented, highly accurate Flow Technology HP-I Series positive displacement flowmeter is ideal for liquid flow applications where process pressure is above 1,000 psig. Applications may include hydraulics, polymers, polyurethanes, plastics and adhesives.

Features


- Up to 3,000 psig operating pressure
- 1/8" to 1" line sizes, larger sizes available
- Reference accuracy ±0.05% of rate
- Only two moving parts
- Bearingless design
- · Easy to install and maintain
- Handles viscosities up to 1,000,000 cP
- Operating temperatures up to 400° F (204° C)
- Wide range of applications
- Non-intrusive sensor
- Up to 1000:1 turndown
- Handles pulsating flow



High Pressure Flowmeters

Protected by one or more U.S. Patents: 4641522, 4815318, 4911010, 4996888, 5027653, Patents Pending


Principle of Operation




Flow Technology positive displacement flowmeters use two rotating, thermoplastic impellers driven by the flowing liquid. Magnets imbedded in the impellers activate a non-intrusive sensor which generates a pulsed output signal. Each pulse represents a known volume of liquid that is captured in between the lobes of the impellers. A K-factor converts the pulses into engineering units for remote data collection and digital display.


Flowmeter Assembly Diagrams

HP01I, HP02I





Dimensions



Specifications

Process Temperature

Up to 400° F (204° C) (Based on impeller materials) Temperatures above 100° F (8° C) reduce pressure rating — consult factory.

Operating Pressure

Standard 3,000 psi (20.68 MPa) (For higher pressure rating, see BL Series product sheet.)

Turndown Ratio

(Ratios based on maximum rated flow)

Low-viscosity fluids 10:1 standard
Medium-viscosity fluids 100:1 standard
High-viscosity fluids Up to 1000:1

Repeatability (Reference Accuracy)

 $\pm 0.05\%$ of rate

Note: Each flowmeter is individually calibrated on a ballistic calibrator traceable to NIST in the flow lab on a liquid representing the specific application.

Accuracy (Linearity)

Typical $\pm 0.5\%$ of rate over upper

80% of full span

With enhanced

signal conditioning Up to $\pm 0.1\%$ of rate over

full turndown range

Output

(Refer to individual product sheets for complete specifications.)

Sensors (1 required per meter)

Hall Effect Sensor: 5–24 VDC square-wave

pulse depending on supply

voltage, 3-wire

Magnetic Pick-up Sensor: 10 mV to 10 V sine-wave

pulse depending on flow

rate, 2-wire

Explosion-proof optional

Signal Conditioners

and Transmitters Refer to individual product

sheets, available from Flow Technology

Materials of Construction

Integral Body 316 stainless steel, standard (Case), Cover(s) Other materials available

Shafts 316 stainless steel, standard Tungsten Carbide, optional

Impellers See Flowmeter Ordering on

last page

O-Rings Viton® or Teflon® standard

Other materials available

Bolts and Nuts

Zinc-plated Grade 8, standard

Other materials and plating

available


Model Specifications

Basic Model No.	Nominal Meter Size	Standard Connection	Maximum Flow Rate		Recommended Mesh Size	Weight	
			GPM	L/min.		lbs.	kg
HP01I	1/8"	1/8" NPT	1	3.79	100	2	0.9
HP02I	1/4"	1/4" NPT	3	11.4	100	8	3.6
HP05I	1/2"	1/2" NPT	12	45.4	80	22	10
HP10I	1"	1" NPT	25	94.6	60	45	20

Dimensions

Basic	A		В		С	
Model No.	inches	mm	inches	mm	inches	mm
HP01I	3.8	97	1.2	30	4.0	102
HP02I	3.8	97	1.8	46	4.0	102
HP05I	5.4	137	2.7	69	6.0	152
HP10I	7.0	178	3.9	99	7.5	191

Model Numbering System



Impeller Normal Temperature Chart

Impeller Material	Operating Temperature	CIP Temperature
PPS	-20° F to +400° F (-29° C to +204° C)	400° F (204° C)
PTFE	-20° F to +250° F (-29° C to +121° C)	250° F (121° C)
UHMWPE	-20° F to +150° F (-29° C to +66° C)	185° F (85° C)

Key

*	Standard Configuration
~	FDA Compliant
CIP	"Clean in Place," a brief cleaning cycle
CF	Consult Factory
+	Not available in size 01 and 02 meters

Material Guide

Name	Description		
316 SS 🗸	316 Stainless Steel		
Buna N 🗸	Nitrile		
Chemraz [®]	Elastomeric PTFE by Greene, Tweed & Co. Inc		
EPDM	Ethylene Propylene		
Kalrez®	Perfluorinated Elastomer by DuPont		
PPS	Polyphenylene Sulfide, Ryton® by Phillips Petroleum		
PTFE	Carbon Filled Polytetrafluoroethylene, Teflon® by DuPont (Impeller Material		
Teflon [®] ✓	Polytetrafluoroethylene, by DuPont (O-Ring Material)		
UHMWPE ✔	Ultra High Molecular Weight Polyethylene		
Viton [®] ✓	Fluorocarbon, by DuPont		

Specifications are for reference only and are subject to change without notice.

Local Representative:





8930 S. Beck Avenue, Suite 107, Tempe, Arizona 85284 USA
Tel: (480) 240-3400 • Fax: (480) 240-3401 • Toll Free: 1-800-528-4225
E-mail: ftimarket@ftimeters.com • Web: www.ftimeters.com